

PMU14G Cut Sheet



NITRA pneumatic push-to-connect fitting, inline pressure indicator, technopolymer body, (1) 1/4in push-to-connect inlet(s), (1) 1/4in push-to-connect outlet(s), 29–145 psi range, green indication.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMU14G>

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Type	Inline pressure indicator
Body Material	Technopolymer
Thread Sealant	No
Fitting Measurement Type	SAE
Inlet Port	(1) 1/4in push-to-connect
Outlet Port	(1) 1/4in push-to-connect
Pressure Range	29–145 psi
Operating Temperature	-4 to +140 °F
Indicating Type	Green indication

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document