

PMU516G Cut Sheet



NITRA pneumatic push-to-connect fitting, inline pressure indicator, technopolymer body, (1) 5/16in (8mm) push-to-connect inlet(s), (1) 5/16in (8mm) push-to-connect outlet(s), 29-145 psi range, green indication.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PMU516G>

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Function	Inline pressure indicator
Body Material	Technopolymer
Fitting Measurement Type	Metric and SAE
Inlet Port	(1) 5/16in (8mm) push-to-connect
Outlet Port	(1) 5/16in (8mm) push-to-connect
Pressure Range	29-145 psi
Operating Temperature	-4 to 140 deg F
Indicating Type	Green indication

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PMU516G.pdf>
See store item page for other formats.