

PNM-CP-4A Cut Sheet



AutomationDirect inductive proximity sensor, tubular, 12mm diameter x 65mm body, bronze-plated brass housing, PNP, N.C. output, 7mm sensing distance, non-flush, 700 Hz switching frequency, IP65 IP66 IP67 IP68 IP69K, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PNM-CP-4A>

Technical Specifications

Brand	AutomationDirect
Item	Proximity sensor
Sensor Type	Inductive
Application	Harsh duty
Shape	Tubular
Housing Size	12mm diameter x 65mm body
Housing Material	Bronze-plated brass
Barrel Type	Threaded
Sensing Method	Extended sensing
Adjustable	No
Number of Wires	3
Switching Output	PNP
Operation Mode	N.C. output

Sensing Distance	7mm
Mounting Type	Non-flush
IO-Link Compatible	No
Switching Frequency	700 Hz
Operating Voltage	10-30 VDC
Operating Temperature	-40 to 85C
Weld Field Immune	No
Chip Immune	No
IP Rating	IP65 IP66 IP67 IP68 IP69K
Connection	Pigtail
Conductor Size	22 AWG
Cable Length	6.5ft/2m
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document