

PNM6-AP-4A Cut Sheet



AutomationDirect inductive proximity sensor, tubular, 12mm diameter x 45mm body, bronze-plated brass housing, PNP, N.O. output, 7mm sensing distance, non-flush, 700 Hz switching frequency, IP65 IP66 IP67 IP68 IP69K, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PNM6-AP-4A>

Technical Specifications

| | |
|-------------------------|---------------------------|
| Brand | AutomationDirect |
| Item | Proximity sensor |
| Sensor Type | Inductive |
| Application | Harsh duty |
| Shape | Tubular |
| Housing Size | 12mm diameter x 45mm body |
| Housing Material | Bronze-plated brass |
| Barrel Type | Threaded |
| Sensing Method | Extended sensing |
| Adjustable | No |
| Number of Wires | 3 |
| Switching Output | PNP |
| Operation Mode | N.O. output |

| | |
|------------------------------|---------------------------|
| Sensing Distance | 7mm |
| Mounting Type | Non-flush |
| IO-Link Compatible | No |
| Switching Frequency | 700 Hz |
| Operating Voltage | 10-30 VDC |
| Operating Temperature | -40 to 85C |
| Weld Field Immune | No |
| Chip Immune | No |
| IP Rating | IP65 IP66 IP67 IP68 IP69K |
| Connection | Pigtail |
| Conductor Size | 22 AWG |
| Cable Length | 6.5ft/2m |
| Includes | Mounting hardware |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E328811 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PNM6-AP-4A.pdf>
See store item page for other formats.