

POC18N Cut Sheet



NITRA pneumatic threaded fitting, pilot operated check valve, rotating, anodized aluminum body, zinc-plated brass threads, (1) #10-32 female UNF to (1) 1/8in female NPT to (1) 1/8in male NPT.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/POC18N>

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Threaded
Fitting Type	Pilot operated check valve
Fitting Function	Rotating
Body Material	Anodized aluminum
Thread Material	Zinc-plated brass
Fitting Measurement Type	SAE
Connection	(1) #10-32 female UNF, (1) 1/8in female NPT and (1) 1/8in male NPT
Operating Pressure	150 psi
Operating Temperature	0 to 160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/POC18N.pdf>
See store item page for other formats.