

POC18N Cut Sheet



NITRA pneumatic threaded fitting, pilot operated check valve, rotating, anodized aluminum body, zinc-plated brass threads, (1) 1/8in female NPT to (1) 1/8in male NPT to (1) #10-32 female threaded connection(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/POC18N>

Technical Specifications

Brand	NITRA
Item	Pneumatic Threaded Fitting
Fitting Type	Pilot operated check valve
Fitting Function	Rotating
Body Material	Anodized aluminum
Thread Material	Zinc-plated brass
Port Connection Info	(1) 1/8in female NPT to (1) 1/8in male NPT to (1) #10-32 female threaded
Operating Pressure	150 psi
Operating Temperature	0 to 160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document