

PR-2609-1 Cut Sheet



Plymouth Rubber VM mastic electrical tape, 4in x 10ft, 600V, self-amalgamating, with liner, black.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PR-2609-1>

Technical Specifications

Brand	Plymouth Rubber
Series	VM
Item	Electrical tape
Backing	PVC
Adhesive	Mastic
Self-Amalgamating	Yes
Liner	Yes
Color	Black
Width	4in
Length	10ft

Thickness	47 mil
Voltage Rating	600V
Elongation At Break	240%
Adhesion To Steel	200 oz/in
Maximum Temperature	194 deg F (90 deg C)
UV Resistant	Yes
Dielectric Strength	330 V/mil
Flame Retardant	No
Manufacturer Part Number	2609

Agency Approvals

RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement