

# PR-2626-1 Cut Sheet



Plymouth Rubber 10 Plyseal mastic electrical tape, 3.75in x 10ft, 600V, self-amalgamating, with liner, black.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PR-2626-1>

## Technical Specifications

|                                 |                      |
|---------------------------------|----------------------|
| <b>Brand</b>                    | Plymouth Rubber      |
| <b>Series</b>                   | 10 Plyseal           |
| <b>Item</b>                     | Electrical tape      |
| <b>Adhesive</b>                 | Mastic               |
| <b>Self-Amalgamating</b>        | Yes                  |
| <b>Liner</b>                    | Yes                  |
| <b>Color</b>                    | Black                |
| <b>Width</b>                    | 3.75in               |
| <b>Length</b>                   | 10ft                 |
| <b>Thickness</b>                | 126 mil              |
| <b>Voltage Rating</b>           | 600V                 |
| <b>Maximum Temperature</b>      | 194 deg F (90 deg C) |
| <b>UV Resistant</b>             | Yes                  |
| <b>Dielectric Strength</b>      | 508 V/mil            |
| <b>Flame Retardant</b>          | No                   |
| <b>Manufacturer Part Number</b> | 2626                 |

## Agency Approvals

|                    |   |
|--------------------|---|
| <b>RoHS Status</b> | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>    | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>       | <a href="#">RoHS Statement</a>                                      |