

PR-3119-5 Cut Sheet



Plymouth Rubber Revere vinyl electrical tape, general purpose, 0.75in x 60ft, 600V, black. Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PR-3119-5>

Technical Specifications

Brand	Plymouth Rubber
Series	Revere
Item	Electrical tape
Duty Rating	General purpose
Backing	PVC
Adhesive	Rubber based
Self-Amalgamating	No
Liner	No
Color	Black
Width	0.75in
Length	60ft
Thickness	7 mil

Voltage Rating	600V
Elongation At Break	220%
Adhesion To Steel	20 oz/in
Minimum Temperature	14 deg F (-10 deg C)
Maximum Temperature	176 deg F (80 deg C)
UV Resistant	No
Dielectric Strength	1200 V/mil
Flame Retardant	Yes
Applicable Standards	<ul style="list-style-type: none">• UL-510• EN 60454-3-1
Quantity per Pack	5
Manufacturer Part Number	3119

Agency Approvals

UL Listed File #	E9880
CSA File #	251817
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement