

PR-3456-1 Cut Sheet



Plymouth Rubber 77 PLYGLAS glass cloth electrical tape, 0.75in x 66ft, 600V, white.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PR-3456-1>

Technical Specifications

Brand	Plymouth Rubber
Series	77 PLYGLAS
Item	Electrical tape
Backing	Glass cloth
Adhesive	Thermosetting rubber based
Self-Amalgamating	No
Liner	No
Color	White
Width	0.75in
Length	66ft

Thickness	7 mil
Voltage Rating	600V
Elongation At Break	5%
Adhesion To Steel	16 oz/in
Maximum Temperature	266 deg F (130 deg C)
UV Resistant	No
Dielectric Strength	350V/mil
Flame Retardant	No
Manufacturer Part Number	3456

Agency Approvals

RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement