

PR-3706-1 Cut Sheet



Plymouth Rubber Premium 37 vinyl electrical tape, professional, 0.75in x 66ft, 600V, white.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PR-3706-1>

Technical Specifications

| | |
|--------------------------|-----------------|
| Brand | Plymouth Rubber |
| Series | Premium 37 |
| Item | Electrical tape |
| Duty Rating | Professional |
| Backing | PVC |
| Adhesive | Rubber based |
| Self-Amalgamating | No |
| Liner | No |
| Color | White |
| Width | 0.75in |
| Length | 66ft |
| Thickness | 7 mil |
| Voltage Rating | 600V |

| | |
|---------------------------------|---|
| Elongation At Break | 260% |
| Adhesion To Steel | 20 oz/in |
| Minimum Temperature | 14 deg F (-10 deg C) |
| Maximum Temperature | 176 deg F (80 deg C) |
| UV Resistant | Yes |
| Dielectric Strength | 1150 V/mil |
| Flame Retardant | Yes |
| Applicable Standards | <ul style="list-style-type: none">• ASTM D-3005, Type I• EN 60454-3-1, Type 11• UL 510• CSA C 22.2 no. 197 |
| Manufacturer Part Number | 3706 |

Agency Approvals

| | |
|-------------------------|---|
| UL Listed File # | E9880 |
| CSA File # | 251817 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |