

# PR-3707-1 Cut Sheet



Plymouth Rubber Premium 37 vinyl electrical tape, professional, 0.75in x 66ft, 600V, brown.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PR-3707-1>

## Technical Specifications

<b>Brand</b>	Plymouth Rubber
<b>Series</b>	Premium 37
<b>Item</b>	Electrical tape
<b>Duty Rating</b>	Professional
<b>Backing</b>	PVC
<b>Adhesive</b>	Rubber based
<b>Self-Amalgamating</b>	No
<b>Liner</b>	No
<b>Color</b>	Brown
<b>Width</b>	0.75in
<b>Length</b>	66ft
<b>Thickness</b>	7 mil
<b>Voltage Rating</b>	600V

<b>Elongation At Break</b>	260%
<b>Adhesion To Steel</b>	20 oz/in
<b>Minimum Temperature</b>	14 deg F (-10 deg C)
<b>Maximum Temperature</b>	176 deg F (80 deg C)
<b>UV Resistant</b>	Yes
<b>Dielectric Strength</b>	1150 V/mil
<b>Flame Retardant</b>	Yes
<b>Applicable Standards</b>	<ul style="list-style-type: none"><li>• ASTM D-3005, Type I</li><li>• EN 60454-3-1, Type 11</li><li>• UL 510</li><li>• CSA C 22.2 no. 197</li></ul>
<b>Manufacturer Part Number</b>	3707

## Agency Approvals

<b>UL Listed File #</b>	E9880
<b>CSA File #</b>	251817
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>