

PR-3711-1 Cut Sheet



Plymouth Rubber Premium 37 vinyl electrical tape, professional, 0.75in x 66ft, 600V, violet.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PR-3711-1>

Technical Specifications

Brand	Plymouth Rubber
Series	Premium 37
Item	Electrical tape
Duty Rating	Professional
Backing	PVC
Adhesive	Rubber based
Self-Amalgamating	No
Liner	No
Color	Violet
Width	0.75in
Length	66ft
Thickness	7 mil
Voltage Rating	600V

Elongation At Break	260%
Adhesion To Steel	20 oz/in
Minimum Temperature	14 deg F (-10 deg C)
Maximum Temperature	176 deg F (80 deg C)
UV Resistant	Yes
Dielectric Strength	1150 V/mil
Flame Retardant	Yes
Applicable Standards	<ul style="list-style-type: none">• ASTM D-3005, Type I• EN 60454-3-1, Type 11• UL 510• CSA C 22.2 no. 197
Manufacturer Part Number	3711

Agency Approvals

UL Listed File #	E9880
CSA File #	251817
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement