

PS116T11-STRH200 Cut Sheet



Schmersal compact limit switch, side rotary lever with plastic roller, 45-degree adjustable head, (1) N.O./ (1) N.C. contact(s), slow action break before make, 31mm wide body, 20-22mm hole spacing, die-cast zinc with plastic base, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PS116T11-STRH200>

Technical Specifications

| | |
|------------------------------|---------------------------------------|
| Brand | Schmersal |
| Item | Limit switch |
| Switch Type | Compact |
| Actuator Type | Side rotary lever with plastic roller |
| Head Type | 45-degree adjustable |
| Contact Type | (1) N.O./ (1) N.C. |
| Action | Slow action break before make |
| Reset | No |
| Body Width | 31mm |
| Mounting Hole Spacing | 20-22mm |
| Material | Die-cast zinc with plastic base |
| IP Rating | IP66 IP67 |
| Operating Temperature | -30 to 80 deg C |
| Connection | 4-pin M12 quick-disconnect |
| Cable Exit | Right |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E57648 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |