

PS116Z11-LR200S200 Cut Sheet



Schmersal compact limit switch, plastic plunger, 45-degree adjustable head, (1) N.O./(1) N.C. contact(s), snap action, 31mm wide body, 20-22mm hole spacing, die-cast zinc with plastic base, pigtail, 6.5ft/2m cable length, right exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PS116Z11-LR200S200>

Technical Specifications

Brand	Schmersal
Item	Limit switch
Switch Type	Compact
Actuator Type	Plastic plunger
Head Type	45-degree adjustable
Contact Type	(1) N.O./(1) N.C.
Action	Snap action
Reset	No
Body Width	31mm
Mounting Hole Spacing	20-22mm
Material	Die-cast zinc with plastic base
IP Rating	IP66 IP67
Operating Temperature	-30 to 80 deg C
Connection	Pigtail
Conductor Size	0.50mm ² (20 AWG)
Cable Length	6.5ft/2m
Cable Exit	Right

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document