

PS116Z11-STRH200 Cut Sheet



Schmersal compact limit switch, side rotary lever with plastic roller, 45-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm hole spacing, die-cast zinc with plastic base, (1) 4-pin M12 quick-disconnect, right exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PS116Z11-STRH200>

Technical Specifications

Brand	Schmersal
Item	Limit switch
Switch Type	Compact
Actuator Type	Side rotary lever with plastic roller
Head Type	45-degree adjustable
Contact Type	(1) N.O./ (1) N.C.
Action	Snap action
Reset	No

Body Width	31mm
Mounting Hole Spacing	20-22mm
Material	Die-cast zinc with plastic base
IP Rating	IP66 IP67
Operating Temperature	-30 to 80 deg C
Connection	(1) 4-pin M12 quick-disconnect
Cable Exit	Right

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/PS116Z11-STRH200.pdf>
See store item page for other formats.