

# PS116Z11-STS200 Cut Sheet



Schmersal compact limit switch, plastic plunger, 45-degree adjustable head, (1) N.O./ (1) N.C. contact(s), snap action, 20-22mm hole spacing, die-cast zinc with plastic base, (1) 4-pin M12 quick-disconnect, bottom exit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PS116Z11-STS200>

## Technical Specifications

|               |                      |
|---------------|----------------------|
| Brand         | Schmersal            |
| Item          | Limit switch         |
| Switch Type   | Compact              |
| Actuator Type | Plastic plunger      |
| Head Type     | 45-degree adjustable |
| Contact Type  | (1) N.O./ (1) N.C.   |
| Action        | Snap action          |
| Reset         | No                   |

|                       |                                 |
|-----------------------|---------------------------------|
| Body Width            | 31mm                            |
| Mounting Hole Spacing | 20-22mm                         |
| Material              | Die-cast zinc with plastic base |
| IP Rating             | IP66 IP67                       |
| Operating Temperature | -30 to 80 deg C                 |
| Connection            | (1) 4-pin M12 quick-disconnect  |
| Cable Exit            | Bottom                          |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E57648                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | None                                   |
| RoHS Status          | Yes (See CE Doc)                       |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/PS116Z11-STS200.pdf>  
See store item page for other formats.