

# PSA-12-120 Cut Sheet



AchieVe PSA series switching power supply, 12 VDC @ 10A/120W, 120/240 VAC nominal input, 1-phase, enclosed, aluminum housing, 35mm DIN rail mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSA-12-120>

## Technical Specifications

<b>Brand</b>	AchieVe
<b>Item</b>	Power supply
<b>Series</b>	PSA
<b>Power Supply Type</b>	Switching
<b>Efficiency</b>	88% @115 VAC, 86% @230 VAC
<b>Output Configuration</b>	Single output
<b>Output</b>	12 VDC @ 10A/120W
<b>Output Voltage Range</b>	10.8-13.2 VDC
<b>Input voltage range</b>	90-264 VAC
<b>Input Voltage Selection Type</b>	Automatic
<b>Number of Input Phases</b>	1
<b>Protection Type(s)</b>	<ul style="list-style-type: none"><li>• overvoltage</li><li>• overcurrent</li><li>• short circuit</li><li>• over-temperature</li></ul>

<b>Remote On/Off</b>	No
<b>Voltage Monitoring</b>	Yes
<b>Enclosure Type</b>	Enclosed
<b>Housing Material</b>	Aluminum
<b>IP Rating</b>	IP20
<b>Mounting</b>	35mm DIN rail
<b>Connector Type</b>	Screw terminals
<b>NEC Class 2</b>	No
<b>Integrated UPS Battery Control</b>	No
<b>Operating Temperature</b>	-30 to 70 deg C

## Agency Approvals

<b>UL Listed File #</b>	E197592
<b>UL Recognized File #</b>	E508040
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/PSA-12-120.pdf>  
See store item page for other formats.