

# PSD25-0P-1450H Cut Sheet



ProSense electronic pressure switch, 75 to 1450 psi set point, 316 stainless steel sensing element, PNP, N.O./N.C. complementary, 1/4in male NPT process connection, 9.6 to 32 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSD25-0P-1450H>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Electronic pressure switch
<b>Setpoint Range</b>	75 to 1450 psi
<b>Sensing Element Material</b>	316 stainless steel
<b>Switching Output</b>	PNP, N.O./N.C. complementary
<b>Process Connection</b>	1/4in male NPT
<b>Operating Voltage</b>	9.6 to 32 VDC
<b>Housing Rating</b>	IP67
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E320431
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>