

PSE05-DC12-40 Cut Sheet



RHINO DC to DC converter, 9.5-36 VDC input, 5.1 VDC output, 8A, 40W, plastic housing, encapsulated, chassis mount, screw terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSE05-DC12-40>

Technical Specifications

Brand	RHINO
Item	DC to DC converter
Input voltage range	9.5-36 VDC
Output Voltage Range	5.1 VDC
Load Current	8A
Output Power	40W
Housing Material	Plastic
Encapsulated	Yes
Mounting	Chassis
Terminal Block Type	Screw terminal
Removable	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	E198298
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PSE05-DC12-40.pdf>
See store item page for other formats.