

# PSE05-DC12-60 Cut Sheet



RHINO DC to DC converter, 9.5-36 VDC input, 5.1 VDC output, 12A, 60W, plastic housing, encapsulated, chassis mount, screw terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSE05-DC12-60>

## Technical Specifications

<b>Brand</b>	RHINO
<b>Item</b>	DC to DC converter
<b>Input voltage range</b>	9.5-36 VDC
<b>Output Voltage Range</b>	5.1 VDC
<b>Load Current</b>	12A
<b>Output Power</b>	60W
<b>Housing Material</b>	Plastic
<b>Encapsulated</b>	Yes
<b>Mounting</b>	Chassis
<b>Terminal Block Type</b>	Screw terminal
<b>Removable</b>	No

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E198298
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>