

PSE05-DC24-60 Cut Sheet



RHINO DC to DC converter, 18-75 VDC input, 5.1 VDC output, 12A, 60W, plastic housing, encapsulated, chassis mount, screw terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSE05-DC24-60>

Technical Specifications

| | |
|-----------------------------|--------------------|
| Brand | RHINO |
| Item | DC to DC converter |
| Input voltage range | 18-75 VDC |
| Output Voltage Range | 5.1 VDC |
| Load Current | 12A |
| Output Power | 60W |
| Housing Material | Plastic |
| Encapsulated | Yes |
| Mounting | Chassis |
| Terminal Block Type | Screw terminal |
| Removable | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E198298 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |