

# PSL-24-BCM240 Cut Sheet



RHINO battery control module, 1 input, 24 VDC nominal input, 23-28 VDC output, 10A, alarm contact for operation monitoring, screw terminals. Requires power supply, 24V battery (user-supplied).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSL-24-BCM240>

## Technical Specifications

Brand	RHINO
Item	Battery control module
Number of Inputs	1
Nominal Input Voltage	24 VDC
Input voltage range	24-28 VDC
Nominal Output Voltage	24 VDC
Output Voltage Range	23-28 VDC
Amperage Rating	10A
Protection Type(s)	<ul style="list-style-type: none"><li>• overvoltage</li><li>• overcurrent</li><li>• reverse polarity</li><li>• over-temperature</li></ul>

Indicating Type	Tri-color LED for status indication and (3) output signals
Alarm Contact for Operation Monitoring	Yes
Remote On/Off	No
Housing Material	Plastic
Mounting	35mm DIN rail
Connector Type	Screw terminals
Requires	Power supply, 24V battery (user-supplied)

## Agency Approvals

UL Listed File #	E197592
UL Recognized File #	E198298
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/PSL-24-BCM240.pdf>  
See store item page for other formats.