

# PSP05-020S Cut Sheet



RHINO SELECT PSP series switching power supply, 5-5.25 VDC output, 4A, 20W, 120/240 VAC or 85-375 VDC nominal input, 1-phase, enclosed, plastic housing, 35mm DIN rail or chassis mount, removable screw terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSP05-020S>

## Technical Specifications

Brand	RHINO SELECT
Item	Power supply
Series	PSP
Power Supply Type	Switching
Efficiency	82% @115 VAC and 230 VAC
Output Configuration	Single output
Output	4A @ 5 VDC/20W
Output Voltage Range	5-5.25 VDC
Input voltage range	85-264 VAC/85-375 VDC
Number of Input Phases	1
Protection Type(s)	<ul style="list-style-type: none"><li>• overvoltage</li><li>• short circuit</li><li>• overload</li></ul>
Remote On/Off	No
Voltage Monitoring	Yes
Enclosure Type	Enclosed
Housing Material	Plastic
IP Rating	IP20
Mounting	35mm DIN rail or chassis
Connector Type	Removable screw terminal
NEC Class 2	No
Integrated UPS Battery Control	No
Operating Temperature	-10 to 70 deg C
Includes	DIN rail insert for panel mounting

## Agency Approvals

UL Listed File #	E197592
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>