

PSP12-DC24-2 Cut Sheet



RHINO DC to DC converter, 18-75 VDC input, 12 VDC output, 2A, 25W, plastic housing, 35mm DIN rail mount, screw terminal, removable. DIN rail insert for panel mounting included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSP12-DC24-2>

Technical Specifications

Brand	RHINO
Item	DC to DC converter
Input voltage range	18-75 VDC
Output Voltage Range	12 VDC
Load Current	2A
Output Power	25W
Housing Material	Plastic
Encapsulated	No
Mounting	35mm DIN rail
Terminal Block Type	Screw terminal
Removable	Yes
Includes	DIN rail insert for panel mounting

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	229285
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document