

PSP24-060C Cut Sheet



RHINO SELECT PSP series switching power supply, 24 VDC @ 2.5A/60W (adjustable), 120/240 VAC or 85-375 VDC nominal input, 1-phase, enclosed, plastic housing, 35mm DIN rail or chassis mount, spring clamp terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSP24-060C>

Technical Specifications

Brand	RHINO SELECT
Item	Power supply
Series	PSP
Power Supply Type	Switching
Efficiency	83% @115 VAC, 86% @230 VAC
Output Configuration	Single output
Output	24 VDC @ 2.5A/60W (adjustable)
Output Voltage Range	24-28 VDC
Input voltage range	85-264 VAC/85-375 VDC
Number of Input Phases	1
Protection Type(s)	<ul style="list-style-type: none">• overvoltage• short circuit• overload

Remote On/Off	No
Voltage Monitoring	Yes
Enclosure Type	Enclosed
Housing Material	Plastic
IP Rating	IP20
Mounting	35mm DIN rail or chassis
Connector Type	Spring clamp terminals
NEC Class 2	No
Integrated UPS Battery Control	No
Operating Temperature	-10 to 70 deg C
Includes	DIN rail insert for panel mounting

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	E198298
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PSP24-060C.pdf>
See store item page for other formats.