

# PSP24-DC12-1 Cut Sheet



RHINO DC to DC converter, 9.5-18 VDC input, 24 VDC output, 1A, 25W, plastic housing, 35mm DIN rail mount, screw terminal, removable. DIN rail insert for panel mounting included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSP24-DC12-1>

## Technical Specifications

<b>Brand</b>	RHINO
<b>Item</b>	DC to DC converter
<b>Input voltage range</b>	9.5-18 VDC
<b>Output Voltage Range</b>	24 VDC
<b>Load Current</b>	1A
<b>Output Power</b>	25W
<b>Housing Material</b>	Plastic
<b>Encapsulated</b>	No
<b>Mounting</b>	35mm DIN rail
<b>Terminal Block Type</b>	Screw terminal
<b>Removable</b>	Yes
<b>Includes</b>	DIN rail insert for panel mounting

## Agency Approvals

<b>UL Listed File #</b>	E197592
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	229285
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>