

PSP24-REM240S Cut Sheet



RHINO redundancy module, 2 inputs, 5/12/24 VDC nominal input, 4-59 VDC output, 8A, removable screw terminals. Requires (2) matched 24 VDC power supplies.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSP24-REM240S>

Technical Specifications

Brand	RHINO
Item	Redundancy module
Number of Inputs	2
Nominal Input Voltage	5/12/24 VDC
Input voltage range	5-60 VDC
Nominal Output Voltage	5/12/24 VDC
Output Voltage Range	4-59 VDC
Amperage Rating	8A
Alarm Contact for Operation Monitoring	No
Active Current Sharing	No
Housing Material	Plastic
Mounting	35mm DIN rail or chassis
Connector Type	Removable screw terminals
Requires	(2) matched 24 VDC power supplies

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PSP24-REM240S.pdf>
See store item page for other formats.