

PSRP-12-DC48-150 Cut Sheet



RHINO PRO DC to DC converter, 18-75 VDC input, 12 VDC output, 12.5A, 150W, aluminum housing, encapsulated, chassis mount, screw terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSRP-12-DC48-150>

Technical Specifications

Brand	RHINO PRO
Item	DC to DC converter
Input voltage range	18-75 VDC
Output Voltage Range	12 VDC
Load Current	12.5A
Output Power	150W
Housing Material	Aluminum
Encapsulated	Yes
Mounting	Chassis
Terminal Block Type	Screw terminal
Removable	No

Agency Approvals

UL Listed File #	None
UL Recognized File #	E198298
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document