

PSUI-0N-4F Cut Sheet



AutomationDirect photoelectric fork sensor, U-frame, die-cast zinc housing, through-beam, infrared light emission, 0-30mm sensing distance, 10-30 VDC operating voltage, selectable light-on/dark-on, NPN, 3-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSUI-0N-4F>

Technical Specifications

Brand	AutomationDirect
Item	Photoelectric fork sensor
Shape	U-frame
Housing Size	50 x 68 x 10mm
IP Rating	IP67
Housing Material	Die-cast zinc
Sensing Method	Through-beam
Operating Voltage	10-30 VDC
Switching Output	NPN
Sensing Distance	0-30mm
Sensitivity	Potentiometer
Operation Mode	Selectable light-on/dark-on
Switching Frequency	2 kHz
Light emission	Infrared
Connection	3-pin M8 quick-disconnect
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document