

# PSUI-0P-6F Cut Sheet



AutomationDirect photoelectric fork sensor, U-frame, die-cast zinc housing, through-beam, infrared, 0-80mm sensing distance, 10-30 VDC operating voltage, selectable light-on/dark-on, PNP, 3-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSUI-0P-6F>

## Technical Specifications

Brand	AutomationDirect
Item	Photoelectric fork sensor
Shape	U-frame
Housing Size	100 x 88 x 10mm
IP Rating	IP67
Housing Material	Die-cast zinc
Sensing Method	Through-beam
Operating Voltage	10-30 VDC

Switching Output	PNP
Sensing Distance	0-80mm
Sensitivity	Potentiometer
Operation Mode	Selectable light-on/dark-on
Switching Frequency	2 kHz
Light Emission (NP)	Infrared
Connection	3-pin M8 quick-disconnect
Additional Information	Purchase cable separately

## Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/PSUI-0P-6F.pdf>  
See store item page for other formats.