

PSUI-0P-9F Cut Sheet



AutomationDirect photoelectric fork sensor, U-frame, die-cast zinc housing, through-beam, infrared, 0-220mm sensing distance, 10-30 VDC operating voltage, selectable light-on/dark-on, PNP, 3-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSUI-0P-9F>

Technical Specifications

Brand	AutomationDirect	Switching Output	PNP
Item	Photoelectric fork sensor	Sensing Distance	0-220mm
Shape	U-frame	Sensitivity	Potentiometer
Housing Size	240 x 153 x 10mm	Operation Mode	Selectable light-on/dark-on
IP Rating	IP67	Switching Frequency	2 kHz
Housing Material	Die-cast zinc	Light Emission (NP)	Infrared
Sensing Method	Through-beam	Connection	3-pin M8 quick-disconnect
Operating Voltage	10-30 VDC	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PSUI-0P-9F.pdf>
See store item page for other formats.