PSV5-15S Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

RHINO PSV series switching power supply, 5 VDC @ 3A/15W, 120 VAC and 240 VAC nominal input, 1-phase, enclosed, plastic housing, 35mm DIN rail mount, screw terminals, NEC Class 2.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/PSV5-15S

Technical Specifications

Brand	RHINO
Item	Power supply
Series	PSV
Power Supply Type	Switching
Efficiency	79% @ 115 VAC and 230 VAC
Output Configuration	Single output
Output	5 VDC @ 3A/15W (adjustable)
Output Voltage Range	5–5.5 VDC
Input voltage range	85–264 VAC
Input Voltage Selection Type	Automatic
Number of Input Phases	1
Protection Type(s)	• overvoltage • short circuit • overload

Remote On/Off	No
Voltage Monitoring	Yes
Enclosure Type	Enclosed
Housing Material	Plastic
IP Rating	IP20
Mounting	35mm DIN rail
Connector Type	Screw terminals
NEC Class 2	Yes
Integrated UPS Battery Control	No
Operating Temperature	-20 to +70 °C

Agency Approvals

UL Listed File #	E197592
UL Recognized File #	E198298
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/PSV5-15S.pdf
See store item page for other formats.