

PSX-CON1 Cut Sheet



Field wireable connector, PG13.5 thread nut 4-pin female axial, accepts cable diameter size 10-12mm, 20 - 14 AWG, screw terminal connection, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PSX-CON1>

Technical Specifications

Item	Field wireable connector
Connector Type	PG13.5 thread nut 4-pin female axial
Cable Diameter Size	10-12mm
Conductor Size	20 - 14 AWG
Terminal Connection	Screw terminal
Shielded	No
IP Rating	IP67

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document