


PT38NAT100 Cut Sheet



NITRA pneumatic tubing, PTFE, natural, 3/8in outside diameter, 0.250in inside diameter, 100ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PT38NAT100>

Technical Specifications

Brand	NITRA
Item	Tubing
Working Fluid	Air or inert gas
Material	PTFE
Color	Natural
Outside Diameter	3/8in
Inside Diameter	0.250in
Working Length	100ft package
Operating Pressure	240 psi
Operating Temperature	-454 to +500 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document