

# PTD25-10-0015H Cut Sheet



ProSense pressure transmitter, 0 to 15 psig range, +/-0.75% accuracy, ceramic sensing element, Viton seal(s), 0-10 VDC analog output, 1/4in male NPT process connection, 16 to 32 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PTD25-10-0015H>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Pressure transmitter
<b>Pressure Range</b>	0 to 15 psig
<b>Accuracy</b>	+/-0.75% of full range
<b>Sensing Element Material</b>	Ceramic
<b>Seal Material</b>	Viton
<b>Analog Output</b>	0-10 VDC
<b>Process Connection</b>	1/4in male NPT
<b>Operating Voltage</b>	16 to 32 VDC
<b>Electrical Connection</b>	4-pin M12 quick-disconnect
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E320431
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>