

PTD25-10-0500H Cut Sheet



ProSense pressure transmitter, 0 to 500 psig range, +/- 0.75% accuracy, ceramic sensing element, Viton seal(s), 0-10 VDC analog output, 1/4in male NPT process connection, 16-32 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PTD25-10-0500H>

Technical Specifications

Brand	ProSense
Item	Pressure transmitter
Pressure Range	0 to 500 psig
Accuracy	+/- 0.75% of full range
Sensing Element Material	Ceramic
Seal Material	Viton
Analog Output	0-10 VDC
Process Connection	1/4in male NPT
Operating Voltage	16-32 VDC
Electrical Connection	4-pin M12 quick-disconnect
Media Type	Liquid and gases
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E320431
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PTD25-10-0500H.pdf>
See store item page for other formats.