

PTD25-20-3000H Cut Sheet



ProSense pressure transmitter, 0 to 3000 psig range, +/- 0.75% accuracy, ceramic sensing element, Viton seal(s), 4-20 mA analog output, 1/4in male NPT process connection, 9.6-32 VDC operating voltage, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PTD25-20-3000H>

Technical Specifications

| | |
|---------------------------------|----------------------------|
| Brand | ProSense |
| Item | Pressure transmitter |
| Pressure Range | 0 to 3000 psig |
| Accuracy | +/- 0.75% of full range |
| Sensing Element Material | Ceramic |
| Seal Material | Viton |
| Analog Output | 4-20 mA |
| Process Connection | 1/4in male NPT |
| Operating Voltage | 9.6-32 VDC |
| Electrical Connection | 4-pin M12 quick-disconnect |
| Media Type | Liquid and gases |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E320431 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PTD25-20-3000H.pdf>
See store item page for other formats.