

PU10MCLR100 Cut Sheet



NITRA pneumatic tubing, ether-based polyurethane, clear, 10mm outside diameter, 6.5mm inside diameter, 100ft package.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PU10MCLR100>

Technical Specifications

Brand	NITRA
Item	Tubing
Working Fluid	Air or inert gas
Material	Ether-based polyurethane
Color	Clear
Outside Diameter	10mm
Inside Diameter	6.5mm
UV stabilized	No
Working Length	100ft package
Operating Pressure	150 psi
Operating Temperature	-40 to +160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document