

# PU14RED500 Cut Sheet



NITRA pneumatic tubing, ether-based polyurethane, red, 1/4in outside diameter, 0.156in inside diameter, 500ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PU14RED500>

---

## Technical Specifications

|                              |                          |
|------------------------------|--------------------------|
| <b>Brand</b>                 | NITRA                    |
| <b>Item</b>                  | Tubing                   |
| <b>Working Fluid</b>         | Air or inert gas         |
| <b>Material</b>              | Ether-based polyurethane |
| <b>Color</b>                 | Red                      |
| <b>Outside Diameter</b>      | 1/4in                    |
| <b>Inside Diameter</b>       | 0.156in                  |
| <b>UV stabilized</b>         | No                       |
| <b>Working Length</b>        | 500ft reel               |
| <b>Operating Pressure</b>    | 180 psi                  |
| <b>Operating Temperature</b> | -40 to +160 deg F        |

---

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |