

PU6MBLK500 Cut Sheet



NITRA pneumatic tubing, ether-based polyurethane, black, 6mm outside diameter, 5/32in (4mm) inside diameter, 500ft reel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PU6MBLK500>

Technical Specifications

Brand	NITRA
Item	Pneumatic Tubing
Material	Ether-based polyurethane
Color	Black
Outside Diameter	6mm
Inside Diameter	5/32in (4mm)
UV stabilized	No
Working Length	500ft reel
Operating Pressure	180 psi
Operating Temperature	-40 to +160 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document