


PX-324-1 Cut Sheet



Protos X temperature input terminal, RTD, 4-channel, 16-bit resolution, input RTD type(s): Pt100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PX-324-1>

Technical Specifications

Brand	Protos X
Item	Input terminal
I/O Module Type	Temperature
Input Signal Type(s)	RTD
Number Of Channels	4
Input RTD Signal Types	Pt100
Input Resolution	16-bit

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/PX-324-1.pdf>
See store item page for other formats.