


# PX-418 Cut Sheet



Protos X analog output terminal, 8-channel, voltage, 12-bit, output voltage signal range(s) of +/- 10 VDC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/PX-418>

## Technical Specifications

<b>Brand</b>	Protos X
<b>Item</b>	Output terminal
<b>I/O Module Type</b>	Analog
<b>Number Of Output Channels</b>	8
<b>Output Signal Type</b>	Voltage
<b>Isolated Channels</b>	No
<b>Output Resolution</b>	12-bit
<b>Output Voltage Signal Range</b>	+/- 10 VDC

## Agency Approvals

<b>UL Listed File #</b>	E157382
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>