


Q0165-1 Cut Sheet



Quabbin control and signal cable, shielded, 2 conductors, 20 AWG, 10-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q0165-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	PLTC, ITC and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	2 conductors
Conductor Size	20 AWG
Conductor Stranding	10-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC

Conductor Insulation Color	Black and red
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.215in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 30 to 99ft = Coil• 100 to 845ft = 14 x 7in Reel• 846 to 1205ft = 14 x 10in Reel• 1206 to 1850ft = 16 x 10in Reel• 1851 to 2580ft = 18 x 10in Reel• 2581 to 3355ft = 18 x 13in Reel• 3356 to 5000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E69976,E70148,E247880
CE	None
CSA File #	LL66965
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement