

Q0170-1 Cut Sheet



Quabbin control and signal cable, shielded, 1 twisted pair, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q0170-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	PLTC, ITC and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	1 twisted pair
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black and red

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.233in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 722ft = 14 x 7in Reel, 723 to 1031ft = 14 x 10in Reel, 1032 to 1596ft = 16 x 10in Reel, 1597 to 2247ft = 18 x 10in Reel, 2248 to 2922ft = 18 x 13in Reel, 2923 to 6276ft = 24 x 17in Wooden Reel, 6277 to 10318ft = 30 x 17in Wooden Reel, 10319 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E247880
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL66965
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement