


Q0170-1 Cut Sheet



Quabbin control and signal cable, shielded, 1 twisted pair, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q0170-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	PLTC, ITC and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	1 twisted pair
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC

Conductor Insulation Color	Black and red
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.233in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 30 to 99ft = Coil• 100 to 720ft = 14 x 7in Reel• 721 to 1025ft = 14 x 10in Reel• 1026 to 1575ft = 16 x 10in Reel• 1576 to 2200ft = 18 x 10in Reel• 2201 to 2860ft = 18 x 13in Reel• 2861 to 5000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E247880
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL66965
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement