

Q0225-1 Cut Sheet



Quabbin control and signal cable, shielded, 1 twisted triad, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q0225-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	PLTC, ITC and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	1 twisted triad
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC

Conductor Insulation Color	Black, white and red
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.245in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 650ft = 14 x 7in Reel• 651 to 930ft = 14 x 10in Reel• 931 to 1425ft = 16 x 10in Reel• 1426 to 1990ft = 18 x 10in Reel• 1991 to 2585ft = 18 x 13in Reel• 2586 to 5000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E247880, E69976, E70148
CSA File #	LL66965, LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement