


Q4100-1 Cut Sheet



Quabbin control and signal cable, unshielded, 4 conductors, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q4100-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	4 conductors
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, white, red and green

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.245in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 653ft = 14 x 7in Reel, 654 to 932ft = 14 x 10in Reel, 933 to 1443ft = 16 x 10in Reel, 1444 to 2032ft = 18 x 10in Reel, 2033 to 2642ft = 18 x 13in Reel, 2643 to 5676ft = 24 x 17in Wooden Reel, 5677 to 9332ft = 30 x 17in Wooden Reel, 9333 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E69976,E118830
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement