


Q4130-1 Cut Sheet



Quabbin control and signal cable, unshielded, 19 conductors, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q4130-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	19 conductors
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Color Code 2

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.465in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 180ft = 14 x 7in Reel, 181 to 260ft = 14 x 10in Reel, 261 to 395ft = 16 x 10in Reel, 396 to 550ft = 18 x 10in Reel, 551 to 720ft = 18 x 13in Reel, 721 to 1605ft = 24 x 17in Wooden Reel, 1606 to 2570ft = 30 x 17in Wooden Reel, 2571 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830, E69976
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement