

Q4175-1 Cut Sheet



Quabbin control and signal cable, shielded, 4 conductors, 18 AWG, 16-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q4175-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	4 conductors
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC

Conductor Insulation Color	Black, white, red and green
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.235in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 30 to 99ft = Coil• 100 to 705ft = 14 x 7in Reel• 706 to 1010ft = 14 x 10in Reel• 1011 to 1545ft = 16 x 10in Reel• 1546 to 2160ft = 18 x 10in Reel• 2161 to 2810ft = 18 x 13in Reel• 2811 to 5000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement